

INSTALLATION MANUAL




559CLT



559CLT—Co-Linear Vent Terminal

Use on following **Valor Fireplaces Models** when installed in or adjacent to existing non-combustible solid-fuel burning fireplace/chimney **ONLY**



3" Inlet & Exhaust Collars. (exhaust collar is slightly longer)


559 CLT

General

The 559 CLT Co-Linear Vent Terminal is approved for use with the Valor direct vent heaters when utilizing 3" side by side flexible co-linear venting into solid fuel burning fireplaces and chimneys (note – co-linear piping cannot be installed into combustible construction). **Ensure proper liner connection by labeling and identifying the "EXHAUST" liner from the heater before connecting to the terminal.**

See the Approved Venting Components' table in the installation manual of the Valor fireplace that is being installed to confirm whether this component can be used with the specific fireplace.

- The 559 CLT is self-flashing when installed onto existing 7" or 8" round factory built metal chimneys (the 7-5/8" dia. collar fits inside of an 8" chimney and outside of a 7").
- When installing onto **existing masonry chimneys** the optional 559 SKF Square Flashing Kit is recommended (see diagram). Add ½" to the height of terminal when installing on square flashing.
- The 559 CLT, may be fastened to the flashing using 3 screws as shown in the diagram at right.
- Liners may be connected to the terminal using sheet metal screws.



Designed and Manufactured by / for Miles Industries Ltd.
North Vancouver, B.C., CANADA V7H 3B1
www.valorfireplaces.com

4000798-03


©2026, Miles Industries Ltd.

Valor® 559CLT



Sortie d'évacuation co-linéaire 559CLT

Utilisez avec les foyers Valor lorsqu'installés dans un foyer ou cheminée existants incombustibles à combustible solides SEULEMENT



559 CLT

Généralités

La sortie d'évacuation co-linéaire 559 CLT est certifiée pour usage avec les foyers à évacuation directe Valor, lorsque deux conduits flex de 3" sont utilisés côte-à-côte pour une évacuation co-linéaire dans une cheminée ou un foyer existant à combustibles solides (note—les conduits co-linéaires ne peuvent pas être utilisés dans une construction faite de matériaux combustibles). Assurez-vous que les conduits flexibles soient branchés au bon endroit en identifiant le conduit "EVACUATION" à partir de l'appareil avant de le brancher à la sortie.

Voir la table d'Accessoires de ventilation certifiés au guide d'installation pour le foyer Valor à installer pour savoir si cette termination peut être utilisée.

- Le 559 CLT ne requiert pas de solin lorsqu'installé dans une cheminée de métal ronde préfabriquée existante de 7" ou 8" (la buse de 7-5/8" de diamètre est placée à l'intérieur d'une cheminée de 8" et à l'extérieur d'une cheminée de 7").
- Lors d'une installation dans une cheminée de maçonnerie existante, le solin carré 559 SKF optionnel est recommandé (voir le schéma).
- Ajoutez 1/2" à la hauteur de la sortie avec l'installation d'un solin carré.
- Le 559 CLT peut être fixé au solin avec 3 vis tel qu'indiqué au schéma de droite.
- Les conduits flexibles peuvent être fixés à la sortie avec des vis à métal.

